

Minimum Requirements for an Off-the-Shelf Tablet

A commercial off-the-shelf tablet must meet the following minimum specifications to work properly with our shaft alignment sensors.

OPERATING SYSTEM	Minimum: Version 13 Recommended: Version 13 (or later)
DISPLAY SIZE	Recommended: 8 inches
RESOLUTION	Recommended: 1280 x 800
NOTE: If you plan to use a device with a different resolution, please consult Fluke Customer Support before purchasing your tablet.	
RADIO	Bluetooth: > 4.2 (Bluetooth Classic) Mandatory for connection with: SensAlign 3; SensAlign 5; SensAlign 7 Bluetooth: > 5.0 (Bluetooth LE) Mandatory for connection with: RotAlign Core; RotAlign Elite
CONNECTIVITY For connection to local Wi-Fi / ARC 4.0 Cloud	Wi-Fi (802.11 ac/b/g/n 2.4 GHz + 5 GHz)
RFID tag function	NFC: Support ISO 15693: I-CODE SLI
INTERFACES	Recommended: USB-C Interface