

Outfit Your Data Center and Save Up to 15%*

Managing a data center is about managing risks and disaster readiness. Having ready access to tools that can help you quickly identify the sources of network failures and outages can keep small incidents from turning into serious ones.

Whether you're installing, reconfiguring, or troubleshooting networks, the new Fluke Networks Data Center Kits provide complete, reliable solutions that support the latest data center technologies.



	Copper Commissioning and Fault Isolation	Fiber (SM+MM) Commissioning and Fault Isolation	Multi-fiber Testing	Fiber Inspection and Cleaning	Live Fiber Detection
Fiber and Copper Commissioning and Troubleshooting Kits	x	x		Single+MPO	x
Fiber Inspection Kits				Single+MPO	x
MPO Maintenance and Troubleshooting Kits			x	MPO only	x

* Save up to 15% compared to US list pricing for items purchased separately.



Fiber and Copper Commissioning and Troubleshooting Kits

Certify performance and troubleshoot copper and fiber cabling. This kit includes what you need to measure performance and isolate problems in copper and fiber (SM and MM) connections. Also includes inspection and cleaning tools for MPO and single fiber end faces plus a tool for determining if a fiber cable or port is live.

DSX2-8000OI	Data Center Fiber & Copper Commissioning and Troubleshooting Kit
DSX2-8000OI/GLD	Data Center Fiber & Copper Commissioning and Troubleshooting Kit + 1yr Gold Support
DSX2-8000OI-NW	Data Center Fiber & Copper Commissioning and Troubleshooting Kit without Wi-Fi

Fiber Inspection Kits

Eliminate the leading cause of fiber failures. Most fiber problems can be prevented by ensuring each fiber end face is clean before plugging it in. Any cable — even new or just-cleaned ones — can be dirty or damaged. The only way to know is to inspect each connector end face, clean it if necessary, then inspect it again to make sure it's really clean. This kit includes inspection cameras and cleaning tools for 1.25 mm and 2.5 mm ferrule devices and ports, plus 8/12/16/24 end face MPOs. Inspection adapters and cleaners are also available for LC-Duplex and VSFF connectors (MDC duplex connectors and MMC multi-fiber connectors).

FI2-7300 DC KIT	Data Center Fiber Inspection Kit
FI2-7300 DCKIT-NW	Data Center Fiber Inspection Kit without Wi-Fi



MPO Maintenance and Troubleshooting Kits

Reduce multi-fiber trunk testing time by 80%. Push one button and our MultiFiber™ Pro tests all 12 fibers in a trunk cable in seconds without the hassle of fan out cords. View loss measurements for individual fibers and polarity in a simple graphical format. Save results in the tester or transfer to LinkWare™ PC for reporting or archiving. Also includes an MPO inspection camera and cleaning tools, plus a tool for detecting a live fiber connection.



MFTK-DC SM Test Kit	MPO Single Mode (1310/1550) Data Center Maintenance & Troubleshooting Kit
MFTK-DC MM/SM Kit	MPO MM/SM (850/1310) Data Center Maintenance & Troubleshooting Kit