

Fluke Power Quality Accessories

Fluke Power Quality accessories are specially designed to enhance and protect Fluke Power Quality/ RPM Full Disclosure™ Power Monitors.

Technical Data

Probes



3601/RPM Crocodile Clip Probe

- Set of 5 replacement alligator voltage clips
- Insulated, nickel plated jaws open up to 3/4" (1.9 cm)

3602/RPM Battery Clip Probe

- Set of 5 battery clip type probes
- Grips conductors up to 3/8" (0.9 cm) wide
- Insulated, nickel plated probe

3605/RPM Stud Type Probe

- 5 syringe-action voltage probes
- Threaded contact for studs/screws up to 3/8" (0.9 cm) wide



3606/RPM Screw on Probe

- 5 screw on type voltage probes
- Interchangeable threaded contacts for 3/8" and 1/2" studs and screws

3607/RPM Bus Bar Probe

- 5 syringe action F type probes
- Adjustable jaw for conductors up to 3/8" (0.9 cm) wide

3608/RPM Plunger Type Probe

- 5 syringe-action voltage probes
- Crocodile jaw for conductors up to 3/8" (0.9 cm) wide
- Plunger style, safety grip operation with insulated jaws



3641/RPM In-Line Fuse

- Set of 5 in-line fuse holders
- Replaceable 1.5" (3.8 cm), 0.25 amp, 200,000 AIC fuse for use with above voltage probes

3650/RPM Replacement Voltage Lead Set for Power Recorder

- US phase color code includes black, red, blue, green, white
- Shrouded 4 mm plug on both ends

Communications

2156/RPM Replacement Ethernet Cable Kit for Power Recorder

- Includes crossover cable, RJ-45 to RJ-45 adapter and patch cable

Cases



4001



4003

4001 Carrying Case

- Rugged canvas bag with heavy duty zipper and straps
- Water resistant with pockets for accessories

4003 Shipping Caddy

- Foam lined, high impact plastic shipping container
- Carrying handle and wheels for shipping, transporting monitor and accessories

4005 Shipping Container

- Foam lined, high impact plastic shipping container
- Carrying handle for transporting monitor and accessories

Mounting

4006 Security Cable

- 6-ft (1.8 m) looped lockable steel cable for securing monitor

4008 Monitor Brackets

- Hardware for permanent mounting to portable Power Recorder

Fluke. *Keeping your world up and running.*

Fluke Corporation

PO Box 9090, Everett, WA USA 98206

Fluke Europe B.V.
PO Box 1186, 5602 BD
Eindhoven, The Netherlands

For more information call:

In the U.S.A. (800) 443-5853 or
Fax (425) 446-5116

In Europe/M-East/Africa (31 40) 2 675 200 or
Fax (31 40) 2 675 222

In Canada (800) 36-FLUKE or

Fax (905) 890-6866

From other countries (425) 446-5500 or

Fax (425) 446-5116

Web access: <http://www.fluke.com>